



**REMOTE-CHANGE HEPA FILTER  
HOUSING Data Sheet:  
24590-HLW-MAD-HOP-00015**

MR No. <b>24590-QL-MRA-MKH0-00002</b>	
Plant Item No. <b>24590-HLW-MK-HOP-HEPA-00008A</b>	Rev No. <b>5</b>

1 Project:	RPP-WTP	Bldg./Rm #	HLW / H-0104	Manufacturer:	Flanders /CSC
2 Project No:	24590	Elevation	0'-0"		
3 Site:	DOE Hanford	Supporting	24590-HLW-MKC-HOP-00009	Manufacturer	*
4 Safety Classification	SC	Calculations	24590-HLW-M6C-HOP-00013	Part No:	
5 Seismic Category	SC-I	Associated	24590-HLW-M6-HOP-00010	Quantity Required	1
6 System No.	HOP	Drawings		Quality Level	Q
7 System Desc.	24590-HLW-3YD-HOP-00001		Spec. for Remote Change HEPA Filter Housing	24590-WTP-3PS-MKH0-T0003	
8 Description:	HLW Vessel Vent / Offgas Melter #2- Secondary "Active" Housing			Environmental Qualification: MILD	See Appendix 1, EQ

**9 DESIGN CONDITIONS**

10 Zone Design Temperature- Summer °F	113	db	Inlet Temp. Design/Normal inlet Air Temp. °F	187	143
11 Site Storage Conditions - Summer °F	113	db	NA	wb	
12 Housing Interior Chemical Exposure	See Note 2				
13 Site Storage Conditions - Winter °F	(-)23	db	Radiological Dose Level per Hr (See Note 2 & 4)	35.4 Rad/Hr	
14 Indoor Design Temperature - Winter °F	59	db	Radiological Dose Level for Facility Life-40yrs (See Note 2 & 4)	1.24 X 10 <sup>7</sup> Rad	

**15 PERFORMANCE RATING**

16 Design Flow Rate (CFM)	4,000		Leakage Rate @ Design Flow &	4 SCFM
17 Min. Operating Pressure (in wc)	(-) 166"		Max Pressure (CFM)	
18 Min. Design Pressure (in wc)	(-) 249"		Assembly Clean Pressure Drop with Filters (in wc)	3.5"
19 Total Filter Openings Required	3		Weight with HEPA Filters (pounds)	*
20 No. Filters per Bank	2		Weight without HEPA Filters (pounds)	*

**21 CONSTRUCTION**

22 NOTE: This housing unit is paired with 24590-					
23 HLW-MK-HOP-HEPA-00008B (Ref. datasheet					
24 24590-HLW-MAD-HOP-00017), orientation as					
25 shown:					
			AIRFLOW »→		
	inlet		Housing 24590-HLW-MK-HOP-HEPA-00008A		outlet
	inlet		Housing 24590-HLW-MK-HOP-HEPA-00008B		outlet
			PLAN VIEW		
26 Design Housing Manufacturer:	Flanders/CSC		Design Housing Model Number:	*	
27 Housing Construction Method:	All Welded		Max. Housing Dim.: (in.) See Note 8	L= *	H= * W= *
28 Housing Material: See Note 12	Type 304L Stainless Steel		Housing Material Gauge:	*	
29 Top Panel Material: See Note 12	Type 304L Stainless Steel		Top Panel Material Gauge:	*	
30 Structural Frame Material: See Note 12	Type 304L Stainless Steel		Structural Frame Features:	*	
31 Inlet Plenum Total Volume:	*		Outlet Plenum Total Volume	*	
32 Inlet Position: (Top/Side)	Side		Outlet Position: (Top/Side)	Side	
33 Inlet Nozzle Dimensions: (inches)	12 in. Diameter, nominal		Outlet Nozzle Dimensions: (inches)	12 in. Diameter, nominal	
34	See Note 5 & 8			See Note 5 & 8	
35 Inlet Connection Type:	Welded		Outlet Connection Type:	Welded	
36 Inlet Flange Bolt Required:	N/A		Outlet Flange Bolts Required:	N/A	
37 Inlet Flange Bolt Size:	N/A		Outlet Flange Bolt Size:	N/A	
38 Inlet Flange Bolt Material:	N/A		Outlet Flange Bolt Material:	N/A	
39 Inlet Flange Gasket Material:	N/A		Outlet Flange Gasket Material:	N/A	
40 Paint and Finish Material:	N/A		Paint and Finish Material Minimum Thickness:		N/A

**41 HOUSING ACCESSORIES**

42 Accessory Provided	Yes	No	Accessory Information	
43 Test w/Inlet Isolation Damper:		X	Damper Provided By:	Others
44 See Note 7			Inlet Isolation Damper Type:	N/A
45			Inlet Isolation Damper Size:	12" Nominal Diameter
46 Inlet Transition Ductwork:		X	Inlet Transition Ductwork	NA
47			Overall Length: (inches)	NA
48			Inlet Transition Smallest	N/A
49			Inside Dimension: (inches)	N/A
50			Inlet Transition Largest	N/A
51			Inside Dimension: (inches)	N/A
52 Inlet Aerosol Test Port Criteria:	X		Challenge Aerosol Connection Type:	*
53 See Note 8			Challenge Aerosol Connection Size:	*
54			Challenge Aerosol Connection Quantity:	*



**REMOTE-CHANGE HEPA FILTER  
HOUSING Data Sheet:  
24590-HLW-MAD-HOP-00015**

MR No. <b>24590-QL-MRA-MKH0-00002</b>
Plant Item No. <b>24590-HLW-MK-HOP-HEPA-00008A</b>
Rev No. <b>5</b>

1	Project:	<b>RPP-WTP</b>	Bldg./Rm #	<b>HLW / H-0104</b>	Manufacturer:	<b>Flanders /CSC</b>	
2	Project No:	<b>24590</b>	Elevation	<b>0'-0"</b>			
3	Site:	<b>DOE Hanford</b>	Supporting	<b>24590-HLW-MKC-HOP-00009 24590-HLW-M6C-HOP-00013</b>	Manufacturer	*	
4	Safety Classification	<b>SC</b>	Calculations		Part No:		
5	Seismic Category	<b>SC-I</b>	Associated	<b>24590-HLW-M6-HOP-00010</b>	Quantity Required	<b>1</b>	
6	System No.	<b>HOP</b>	Drawings		Quality Level	<b>Q</b>	
7	System Desc.	<b>24590-HLW-3YD-HOP-00001</b>		Spec. for Remote Change HEPA Filter Housing	<b>24590-WTP-3PS-MKH0-T0003</b>		
8	Description:	<b>HLW Vessel Vent / Offgas Melter #2- Secondary "Active" Housing</b>			Environmental Qualification: MILD See Appendix 1, EQ		

<b>9 HOUSING ACCESSORIES (continued)</b>							
10	Accessory Provided	Yes	No	Total Number of Viewing Ports Required:	N/A		
11	Inlet Viewing Ports		X	Inlet Viewing Port Type:	N/A		
12				Inlet Viewing Port Locations:	N/A		
13				Inlet Viewing Port	N/A	Width	
14				Dimensions: (inches)	N/A	Length	
15	Internal Fire Suppression:		X	Fire Suppression System Description:	N/A		
16				Accessory Information	1 per bank		
17	Vacuum-Relief Vent Assembly:	X		Number Required:	*		
18				Vacuum-Relief Vent Assembly Setpoint:	*		
19				Vacuum-Relief Vent Assembly Manufacturer:	*		
20				Vacuum-Relief Vent Model Number:	N/A		
21	Test w/Outlet Isolation Damper:		X	Damper Provided By:	Others		
22	See Note 7			Outlet Isolation Damper Type:	N/A		
23				Outlet Isolation Damper Size:	N/A		
24	Outlet Transition Ductwork:		X	Outlet Transition Ductwork Overall	NA		
25				Length: (inches)	N/A		
26				Outlet Transition Smallest Inside	N/A		
27				Dimension:(inches)	N/A		
28				Outlet Transition Largest Inside	N/A		
29				Dimension: (inches)	N/A		
30	Outlet Aerosol Test Port Criteria:	X		Challenge Aerosol Connection Type:	*		
31	See Note 8			Challenge Aerosol Connection Size:	*		
32				Challenge Aerosol Connection Quantity:	N/A		
33	Outlet Viewing Ports:		X	Total Number of Viewing Ports Required:	N/A		
34				Outlet Viewing Port Type:	N/A		
35				Outlet Viewing Port Locations:	N/A	Width	
36				Outlet Viewing Port	N/A	Length	
37				Dimensions: (inches)	N/A		
38	Differential Pressure Taps:	X		Differential Pressure Tap Size: (inches)	1/2-in. (See Note 3)		
39	Drain Connection: See Note 9	X		Drain Connection Size: (inches)	1 1/2-in. (See Note 9)		
40	Drain Connection Valve:		X	Drain Connection Valve Size: (inches)	N/A		
41				PVC Safe Change Bag Type:			

<b>42 UTILITY REQUIREMENTS</b>							
43	Electrical: (volts/phase/hertz)	N/A					
44	Compressed Air:	N/A					
45	Instrumentation Taps:	3/4-inch SW					
46	Pressure/Leak Test Ports	*					
47	Air/Aerosol Mixing Test Ports	*					
48	NOTE: See Appendix 2 for locations of test ports. SELLER to provide aerosol injection and sampling lines from housing penetration to connection point located on Appendix 2 sketches. Aerosol lines shall be routed outside housing through box stiffeners, so as not to project outside the housing envelope. Aerosol injection and sampling lines shall be stainless steel pipe per specification 24590-WTP-3PB-P000-TS11Z, or equal.						
49							
50							
51							
52							
53							



**REMOTE-CHANGE HEPA FILTER  
HOUSING Data Sheet:  
24590-HLW-MAD-HOP-00015**

MR No.

**24590-QL-MRA-MKH0-00002**

Plant Item No.

**24590-HLW-MK-HOP-HEPA-00008A**

Rev No.

**5**

1	Project:	RPP-WTP	Bldg./Rm #	HLW / H-0104	Manufacturer:	Flanders /CSC
2	Project No:	24590	Elevation	0'-0"		
3	Site:	DOE Hanford	Supporting	24590-HLW-MKC-HOP-00009	Manufacturer	*
4	Safety Classification	SC	Calculations	24590-HLW-M6C-HOP-00013	Part No:	
5	Seismic Category	SC-I	Associated	24590-HLW-M6-HOP-00010	Quantity Required	1
6	System No.	HOP	Drawings		Quality Level	Q
7	System Desc.	24590-HLW-3YD-HOP-00001	Spec. for Remote Change HEPA Filter Housing		24590-WTP-3PS-MKH0-T0003	
8	Description:	HLW Vessel Vent / Offgas Melter #2- Secondary "Active" Housing			Environmental Qualification: MILD See Appendix 1, EQ	

9 Notes:

10 1.) Vendor to fill in data with (\*) asterisk.

11 2.) **Service Conditions, HOP OFF-GAS:** Reference Calc. 24590-WTP-M3C-HOP-00001, Melter Offgas and Liquid Effluent Definition, Stream No.HV232 (First HEPA Inlet Gas):

12 **The constituents off-gas (Based on a 3.5 MT/day melter basis):**

13 **Chemicals:**

14 N <sub>2</sub> = 69.6%	CO = 4.82E+01 mg/m <sup>3</sup>	P = 2.21E-04 mg/m <sup>3</sup>	Dose:	Temperature = 61°C
15 O <sub>2</sub> = 18.5%	NO <sub>x</sub> = 1.04E+03 mg/m <sup>3</sup>	NH <sub>3</sub> = 3.60E+01 mg/m <sup>3</sup>	Alpha = 2.26E-03 Bq/m <sup>3</sup>	Dew Pt. Temp = 43.9°C
16 Ar = 0.8%	SO <sub>x</sub> = 1.64E+01 mg/m <sup>3</sup>	Entrain of Solids = 3.95 mg/m <sup>3</sup>	Beta/Gamma <sup>(1)</sup> = 3.41E+01 Bq/m <sup>3</sup>	Density = 0.881 kg/m <sup>3</sup>
17 CO <sub>2</sub> = 0.6%	Cl = 5.52E-02 mg/m <sup>3</sup>		H-3 = 7.95E+03 Bq/m <sup>3</sup>	Therm.Conduct = 27.81 mW/m-c
18 H <sub>2</sub> O = 10.4%	F = 8.07E-02 mg/m <sup>3</sup>		C-14 = 3.87E+03 Bq/m <sup>3</sup>	Heat Cap 1.07 kJ/kg-C
19			I-129 = 4.32E-02 Bq/m <sup>3</sup>	Relative Humidity = 44.4%
20				Ave. Mole Wt. = 27.9 g/mol
21			(1) Beta/Gamma dose excludes Tritium, Carbon-14, and Iodine.	Viscosity = 19.54 uPa-s
22				Pressure = 875 mbar

22 3.) **Differential Pressure Tap:** 1/2" Socket Weld, T-304L SS Half Coupling. Size of the hole penetrating housing pressure boundary at 1/8" diameter.

23 4.) **Radiation Dose Rates** for HLW R5 room H-0104 (Filter Cave), See CCN: 152094, Ref. Calc. 24590-HLW-Z0C-30-00016, Table 7-10.

24 5.) The thickness for the 12" dia. inlet / outlet connections on the filter housing and the ductwork supplied between the primary and secondary filter housings shall be 0.18" thick (pipe per ASTM A312 or rolled and welded plate per A240).

25 6.) N/A denotes "Not Applicable".

26 7.) **HEPA Housing** has been credited to perform following a seismic event. Therefore, the design is required to be Seismic Qualification Tested (i.e., shaker table test) in accordance with 24590-WTP-3PS-MKH0-T0001. During shop test, contractor may use a temporary valve or blank -off plate.

27 **Min. Housing Filter System Efficiency:** >= 99.7% (inclusive margin) per ASME AG-1 TA-4634, prior to, during and following shake test.

28 Observe and note efficiency reading on photometer during test.

29 **HEPA Filter Seismic Qualification:** ASME AG-1 FK-4300 and Equipment Qualification Data Sheet (Appendix 1 and Attachment A).

30 **Pressure Boundary and Filter Sealing Surface Allowable Leakage:** < 0.0005 scfm/cu. ft of test volume following seismic test.

31 8.) Aerosol test ports include injection and sampling at each stage. See vendor submittal 24590-QL-POA-MKH0-00002-07-00100, 00111, 00112 and 00118 for HOP HEPA Filter Housing end panel assembly details and overall dimension.

32 9.) **Drain connection:** 1 1/2-in. NPT T-304L SST pipe nipple with cap, drain at low point in the plenum.

33 10.) **Sealing materials and mechanism** shall comply with ASME AG-1.

34 11.) **Contents of this document** are "Dangerous Waste Permit Affecting".

35 12.) **Low carbon content alloy steel:** "L" designated materials, i.e., Type 304L stainless steel, with a maximum carbon content of 0.030% shall be used for pressure boundary materials (exposed to the offgas stream) that will be welded. Type 304 SST may be substituted for items such as fasteners that will not be welded. Alternate materials may be proposed and accepted by the Buyer using the design submittal process.

36 **Remarks:** Modifications to the content of this datasheet shall be made by vendor submittal and are subject to Buyer's permission to proceed.

37 **FOR AS-BUILT INFORMATION REFER TO VENDOR SUBMITTALS.**

38 Blank data fields are not required to be completed.

44	SAFETY SCREENING/EVALUATION REQUIRED? IF YES PER 24590-WTP-GPP-SREG-002, E&NS SIGNATURE REQUIRED BELOW			YES = X	NO =		
46	5	3/1/10	Revised note 7 and added shaker table test notification. Updated attached EEQ (Appendix 1) per latest templates and with revised ISRS data and curves from coupled analysis. HEPA Housing overall dimension per F/CSC.	<i>[Signature]</i>	<i>[Signature]</i>	<i>[Signature]</i>	<i>[Signature]</i>
47			<del>Incorporated DCN 24590-WTP-MON-M80T-00001</del>				
48	4	9/24/2009	Added note 11 per DCN 24590-HLW-MAN-HOP-00001 & note 12, attached EEQ (Appendix 1) with RRS curves from coupled analysis and Safety Screening Evaluation. Revised Safety Class to SC and Quality Level to Q. Consolidate attachment "B" into Note 2. Revised Note 3 and 4, and added housing overall dimensions. Revised note 8 per vendor submittal 24590-QL-POA-MKH0-00002-07-00100, 111 and 112.	<i>[Signature]</i>	<i>[Signature]</i>	<i>[Signature]</i>	<i>[Signature]</i>
49				R.K. Ramos	C. Meng	J. Tuck	L. Solis
50	3	4/4/2005	Revised note 5 to incorporate 24590-WTP-SDDR-PROC-05-00290 disposition, room no., calc. no., and radiological dose. Deleted Attachment A.	M. Ordone		A. Jocson	L. Solis
51	2	12/2/2003	Revised the Design Conditions, Performance Rating Sections and Seismic Category to SC-I and Quality Level	M. Ordone		DEG	Hadi Jalali
52	1	9/8/2003	Revised the Design Conditions and Performance Rating sections	M. Ordone		D.E.Green	J. Sanders
53	0	10/22/2002	Issued for Purchase	David Royer		A.C.Tan	J. Sanders
54	Rev	Date	Description	Originator	E&NS	Checker	Reviewer



**APPENDIX 1  
REMOTE CHANGE HEPA FILTER HOUSING  
EQUIPMENT QUALIFICATION Data Sheet:  
24590-HLW-MAD-HOP-00015**

MR No.

**24590-QL-MRA-MKH0-00002**

Plant Item No.

**24590-HLW-MK-HOP-HEPA-00008A**

Rev No.

**5**

1	<b>EQUIPMENT IDENTIFICATION:</b>				
2	Full Component Tag Number or BNI Stock Code Number	24590-HLW-MK-HOP-HEPA-00008A			Safety Classification
3	Equipment Datasheet Number	24590-HLW-MAD-HOP-00015			<input checked="" type="checkbox"/> SC <input type="checkbox"/> SS
4					<input type="checkbox"/> APC-PAM
5	Description	HLW Vessel Vent / Melter #2 Offgas Vent is a Primary and Secondary HEPA Filter Housing configuration with a remote operated Inlet / Outlet dampers (By Others). There are two parallel assemblies of offgas filters containing two stages of HEPA filters in series to perform high efficiency removal of sub-micron particulates from the heated offgas.			Seismic Category
6					<input checked="" type="checkbox"/> SC-I <input type="checkbox"/> SC-II
7					<input type="checkbox"/> SC-III <input type="checkbox"/> SC-IV
8					<input type="checkbox"/> SC-III Seismic Interaction only
9	Location (Facility / Building and Room No.)	HLW HOP Primary HEPA Filter Housing 24590-HLW-MK-HOP-HEPA-00008A is located inside Room H-104, at EL. 0'-0".			
10	Safety Function(s)	Provide confinement and protection against crush/impact events. To provide filtration of the offgas to prevent releases that may result in consequences to the public, co-worker, and facility worker above RES (Rad. Exposure Std.) in the SRD (Safety Requirement Doc.). Source: 24590-WTP-PSAR-ESH-01-002-04 Section: 4.3.20.1			
11					
12					
13	Equipment Safety Function Type	<input checked="" type="checkbox"/> Passive Mechanical	<input type="checkbox"/> Active Mechanical	<input type="checkbox"/> Electrical	
14	Seismic Safety Function	Seismic Operability Requirements			
15	<input checked="" type="checkbox"/> Yes <input type="checkbox"/> No	<input checked="" type="checkbox"/> During Seismic Event	<input checked="" type="checkbox"/> After Seismic Event	<input type="checkbox"/> None	
16					
17	<b>EQUIPMENT ENVIRONMENTAL QUALIFICATION ( EEQ )</b> (Parameter values stated in this section do not include process conditions or operationally induced conditions)				
18	Classification of Environment	<input checked="" type="checkbox"/> Mild	<input type="checkbox"/> Harsh	Qualified Life (years)	<input checked="" type="checkbox"/> 40 <input type="checkbox"/> Other
19	Parameters Type / Units	Parameter Value	Parameter Duration (number)	Duration Units	WTP Source Document Number
20					
21	<b>Normal Ambients</b>				
22	High Temperature (°F)	113	Note 20	40 Years	24590-HLW-U0D-W16T-00001
23	Low Temperature (°F)	59	Note 21	N/A	24590-WTP-DB-ENG-01-001, Table 12-1 (Plant rooms)
24	High Relative Humidity (%RH)	100 Condensing	Note 22	N/A	24590-HLW-U0D-W16T-00001
25	Low Relative Humidity (%RH)	5	Note 22	N/A	24590-HLW-U0D-W16T-00001
26	High Pressure (in.-w.g.)	0	Note 23	N/A	24590-HLW-U0D-W16T-00001
27	Low Pressure (in.-w.g.)	(-)1.4	Note 23	N/A	24590-HLW-U0D-W16T-00001
28	Radiation Dose Rate (mRad/hr)	35,400	40	Years ( Note 24- A )	24590-HLW-U0D-W16T-00001 (24590-HLW-Z0C-30-00016, See CCN 152094)
29	Plant / Process Induced Vibration	<input type="checkbox"/> Yes	<input checked="" type="checkbox"/> No		
30	Additional Normal Information:	None			
31					
32	<b>Abnormal Ambients</b>				
33	High Temperature (°F)	126	8	hours/yr	24590-HLW-U0N-W16T-00001 (For Duration See: 24590-HLW-U0D-W16T-00001, 1.4C)
34	Low Temperature (°F)	40	Note 21	N/A	24590-HLW-U0D-W16T-00001
35	High Relative Humidity (%RH)	100 Condensing	Note 22	N/A	24590-HLW-U0D-W16T-00001
36	Low Relative Humidity (%RH)	6	Note 22	N/A	24590-HLW-U0N-W16T-00001
37	High Pressure (in.-w.g.)	4	Note 23	N/A	24590-HLW-U0D-W16T-00001
38	Low Pressure (in.-w.g.)	(-)6.7	Note 23	N/A	24590-HLW-U0D-W16T-00001
39	Radiation Dose Rate (mRad/hr)	35,400	0	Years ( Note 24- A )	24590-HLW-U0D-W16T-00001 (24590-HLW-Z0C-30-00016, See CCN 152094)
40	Exposure to Wet Sprinkler System	<input type="checkbox"/> Yes	<input checked="" type="checkbox"/> No	NA	
41	Additional Abnormal Information:	None			
42					



**APPENDIX 1**  
**REMOTE CHANGE HEPA FILTER HOUSING**  
**EQUIPMENT QUALIFICATION Data Sheet:**  
**24590-HLW-MAD-HOP-00015**

MR No.  
**24590-QL-MRA-MKH0-00002**

Plant Item No.  
**24590-HLW-MK-HOP-HEPA-00008A**

Rev No.  
**5**

1	Parameters Type / Units	Parameter Value	Parameter Duration (number)	Duration Units	WTP Source Document Number
2	<b>Design Basis Events (DBE) Ambients</b>				
3	High Temperature (°F)	135	1000	hours	24590-HLW-U0N-W16T-00001 (For Duration See: 24590-HLW-U0D-W16T-00001, 1.4D)
4	Low Temperature (°F)	40	Note 21	N/A	24590-HLW-U0D-W16T-00001
5	High Relative Humidity (%RH)	100 Condensing	482	hours	24590-HLW-U0D-W16T-00001
6	Low Relative Humidity (%RH)	6	1000	hours	24590-HLW-U0N-W16T-00001
7	High Pressure (in.-w.g.)	4	1000	hours	24590-HLW-U0D-W16T-00001
8	Low Pressure (in.-w.g.)	(-)6.7	1000	hours	24590-HLW-U0D-W16T-00001
9	Radiation Dose Rate (mRad/hr)	35,400	0	hours	24590-HLW-U0D-W16T-00001 (24590-HLW-Z0C-30-00016, See CCN 152094)
10	Submergence	<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No		hours	See Note 16
11	Chemical/Spray Exposure	<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No		hours	24590-HLW-U0D-W16T-00001
12	Additional DBE Information	Note 25			
13					
14					
15					
16					
17					
18	<b>DBE Chemical Exposure Details</b>				
19	DBE Chemical Types/Concentration	NONE			
20					
21					
22					
23	<b>Electrical Interfaces Supporting the Safety Function</b>				
24	Power Supply Voltage (VAC, VDC)	NA			
25	Power Supply Frequency (Hz)	NA			
26	Power Connection Method	NA			
27	I / O Signals to /from Equipment	NA			
28	I / O Connection Method	NA			
29					
30	<b>Mechanical Interfaces</b>				
31	Mounting Configuration (orientation)	* Note 13			
32	Mounting Method (bolts, welds, etc)	* Note 13			
33	Auxiliary Devices	* Note 13			
34					
35	<b>Equipment Seismic Qualification ( ESQ )</b>				
36	<b>Parameters</b>	<b>Title</b>	<b>References/Documents Number</b>	<b>Version/Revision</b>	<b>Remarks</b>
37	WTP Seismic Design Specification	Seismic Qualification of Seismic Category I/II Equip. and Tanks	24590-WTP-3PS-SS90-T0001	2	N/A
39	Specified Seismic Load Parameters	HLW Filter Cave Coupled Structural Analysis	24590-HLW-S0C-S15T-00108	0B	See Note 18 and Attachment A
40					
41					
42					
43					
44					
45					
46					
47					
48					



**APPENDIX 1**  
**REMOTE CHANGE HEPA FILTER HOUSING**  
**EQUIPMENT QUALIFICATION Data Sheet:**  
**24590-HLW-MAD-HOP-00015**

MR No.  
**24590-QL-MRA-MKH0-00002**

Plant Item No.  
**24590-HLW-MK-HOP-HEPA-00008A**

Rev No.  
**5**

**Equipment Qualification Notes and Additional Information**

**Notes: Continuation from page 3, Data Sheet:**

13. \* Data to be provided by SELLER through the submittal process as required on the G-321-E form.
14. Note Deleted.
15. Note Deleted See Note 24 A & B.
16. Equipment submergence shall reference to the room postulated water depths and the actual equipment elevation from the floor. Remote HEPA Filter Housing are supported by structural steel and elevated above the room flood heights of 1.58 ft.
17. Remote HEPA Filter Housing needs to be qualified for the external (Room H-0104 (R5/C5)) and internal (Off-gas constituents, See Note 2), significant environment differences such as in room temperatures, pressures and radiation dose level (Rad dose could be above 34,500 mRad/hr) that may affect the short term or long term ability of the equipment to perform its safety functions. The interrelationship between external/internal of the Remote HEPA Filter Housing environments has not been analyzed so the difference identified in the EQD represent potential for extreme.
18. Nozzle loads and in-structure response spectra (ISRS) are provided by CSA (see Att.A). ISRS are suitable for seismic qualification of the filter boxes by analysis. They are also provided for testing of the filters, but do not include a 1.4 factor for testing, or any other conservatism. The curves are provided for 4% and 5% damping. ISRS data points are at the bottom support points of the boxes. In the nozzle load data, live loads related to civil structural steel and are not directly involved with ducting or filter housing. The "thermal, normal" case is intended for combination with seismic (if required). The "thermal, off-normal" applies to post-DBE conditions. Nozzle ISRS data point locations are on the nozzle centerline at the filter housing box face. Nozzle loads in Att. A do not include factors for conservatism. Magnitudes are enveloping for all nozzles. Load components in Att. A are defined as follows:
 

P = Axial Load	T = Torsion
V2 = Shear along minor axis (vertical)	M2 = Moment about minor axis
V3 = Shear along major axis (horizontal)	M3 = Moment about major axis
19. **DOE Radioactive Materials Disclaimer:**  
 Please note that source, special nuclear and byproduct materials, as defined in the Atomic Energy Act of 1954 (AEA), are regulated at the US Department of Energy (DOE) facilities exclusively by DOE acting pursuant to its AEA authority. DOE asserts, that pursuant to AEA, it has sole and exclusive responsibility and authority to regulate source, special nuclear, and byproduct materials at DOE-owned nuclear facilities. Information contained herein on radionuclides is provided for process description purposes only.
20. For thermal aging, the high normal temperature shall be assumed to subsist for 40 years less the duration of the high abnormal temperature. For any lesser qualified life, the normal and abnormal condition durations shall be assigned proportionally. The abnormal temperature is stated to subsist for a certain number of hours per year. It shall be taken to subsist for this number of hours for each year of the qualified life.
21. The ability to provide the safety function at the low normal temperature, the low abnormal temperature or the low DBE temperature (whichever be the lowest) shall be established by test, analysis, or operating experience. The thermal aging at these respective low temperatures will be conservatively covered by the thermal aging per note 20 above. Therefore, no duration is assigned for the low temperatures.
22. The ability to provide the safety function at the extremes of the normal and abnormal humidity conditions, taking into consideration the high and low normal, and high and low abnormal, shall be established by test, analysis, or operating experience. No duration is assigned for the normal and abnormal humidity conditions.
23. If the performance of the safety function of the equipment is affected by ambient pressure, the ability to provide the safety function at the extremes of the normal and abnormal pressure conditions, taking into consideration the high and the low normal and the high and low abnormal pressures, shall be established by test, analysis, or operating experience. No duration is assigned to the normal and abnormal pressure conditions.
24.
  - A. If the abnormal radiation dose rate is the same as the normal radiation dose rate, the normal radiation dose rate shall be assumed to subsist for 40 years, or any lesser qualified life, and the duration of the abnormal radiation dose rate is "0."
  - B. If the abnormal radiation dose rate is higher than the normal radiation dose rate, the abnormal radiation dose rate shall be assumed to subsist for 40 years, or any lesser qualified life, and the duration of the normal radiation dose rate is "0."
25. The DBE conditions shall be taken to subsist for the stated number of hours following the qualified life of the equipment.
26. The values stated in this EQD are the ambients and do not include the thermodynamic and radiation conditions imposed by the process fluids, self-heating, etc. The data pertaining to process fluid and service induced parameters are to be taken into account where significant, such as in thermal aging analyses. These data can be obtained from the equipment data sheets or the Equipment Specification.
27. Equipment that is to be installed in inaccessible locations must be qualified to a 40-year life without the need for maintenance or replacement.



**ATTACHMENT A**  
**REMOTE CHANGE HEPA FILTER HOUSING**  
**EQUIPMENT QUALIFICATION Data Sheet:**  
**24590-HLW-MAD-HOP-00015**

MR No.

**24590-QL-MRA-MKH0-00002**

Plant Item No.

**24590-HLW-MK-HOP-HEPA-00008A**

Rev No.




**5**

**In-Structure Response Spectra (ISRS) and Nozzle Load: Based on 24590-HLW-SOC-S15T-00108, Rev. B**

System	Load Case	P / Kip	V2 / Kip	V3 / Kip	T / Kip-in	M2 / Kip-in	M3 / Kip-in
Nozzle Load for HOP HEPA Housing	DL ( Dead + Live )	0.12	2.94	0.04	6.7	1.2	5.4
	To (thermal, normal)	0.86	1.87	0.22	13.2	1.8	5.3
	Ta (thermal, off-normal & Post DBE)	2.19	3.92	0.38	28.0	2.7	11.5
	E (Seismic)	0.56	1.13	0.51	8.7	2.4	3.0

See Note 18 for definition of load components (P, V2, V3, T, M2, & M3), load cases, and conservatism factors.

**Filter Box Support ISRS**



**Filter Box Support ISRS Data:**

Direction:	EW	EW	NS	NS	Vert	Vert
Damping:	4%	5%	4%	5%	4%	5%
Freq, Hz	Accel, g	Accel, g	Freq, Hz	Accel, g	Accel, g	Accel, g
0.30	0.13	0.12	0.30	0.13	0.12	0.105
0.94	0.60	0.55	1.00	0.64	0.60	0.32
2.00	0.88	0.85	1.90	0.85	0.80	0.77
5.30	0.88	0.85	6	0.85	0.80	0.82
12	0.53	0.50	10	0.85	0.80	0.80
23	0.53	0.50	12	1.10	1.00	0.68
26	0.77	0.67	14	1.96	1.66	0.43
35	0.77	0.67	20	1.96	1.66	0.70
43	0.37	0.35	31	0.96	0.70	0.70
50	0.37	0.35	50	0.48	0.45	



**APPENDIX 2**  
**REMOTE CHANGE HEPA FILTER HOUSING**  
**Nozzle Location Sketch for Datasheet:**  
**24590-HLW-MKD-HOP-00015**

MR No.


**24590-QL-MRA-MKH0-00002**

Plant Item No.


**24590-HLW-MK-HOP-HEPA-00008A**

Rev No.

**5**



**ELEVATION VIEW OF HOP-HEPA-00008A**



**Nozzle Designations:**

- N05: Injection port
- N06: Upstream sample
- N07: Upstream static pressure.
- N08: Downstream static pressure
- N09: Downstream sample
- N010: Housing outlet